

## Nucleus Megatron® NV-200-LF-2PS

### Dual Nucleus Digital Mixing Valve Recirculation Assembly

#### 1.0 Nucleus Digital Mixing Valve

- A. Mixing Valve shall be Digital and comply with National Low Lead Laws @ < .25% Lead
- B. NV-200-LF-2PS shall have 4" inlet/outlet and 2" return Loop piping connections with integral stop/check valves on each NV-200-LF, deliver mixed water flow of 346 GPM @ 30 PSI Pressure Drop and maintain temperature with .25 GPM flow from the domestic hot water loop
- C. Each NV-200-LF shall have all the following operational capabilities:
1. 1X per day shuttle sweep designed to prevent scale buildup on internal mechanical components
  2. +/- 2°F water temperature control
  3. 2°F minimum inlet to outlet water temperature differential
  4. Automatic shutoff of hot water upon cold water inlet supply failure
  5. Automatic shutoff of cold water upon hot water inlet supply failure
  6. Maintain last control position in the event of power failure or be equipped with UPS standby power for approximately 2 hour run time
  7. Programmable set point range of 65-180°F (18-82°C)
  8. Programmable thermal disinfection mode
  9. Programmable hi/low temperature alarm display
  10. Primary printed circuit board capable of displaying up to 4 temperature sensors, and 2 pressure sensors with plug-in expansion board capabilities for 4 additional temperatures, 1 flow and 1 configurable channel (flow or pressure)
- D. Each NV-200-LF shall have all of the following connectivity capabilities:
1. Relay Rating: 30V DC, SELV, LPS, or Class 2, 2Amp MAX, 60 W, NO Only
  2. 2-line, 16-character LED display with plumbing system overlay diagram and 6 LED status indicators providing for ease of identification of system status
  3. Six (6) standard Protocol Languages including BACnet IP & MS/TP, Modbus RTU & TC/IP, Metasys N2 by JCI, Ethernet/IP with BACnet Testing Laboratories approval
  4. Local keypad user interface or laptop connectivity via RS485 Serial Port for temperature adjustment and commissioning
- E. Each NV-200-LF shall be compliant with ASSE standard 1017 and CSA B125/cUPC and so certified and identified
- F. Each NV-200-LF shall be cULus listed and identified
- G. Nucleus Megatron NV-200-LF-2PS shall be strut mounted with 4" inlet and outlet piping and 2" return loop piping and include 3/4" outlet test connection, (2) 1-1/4" check valves and full port ball valves, a 2" check valve and full port ball valve, 3/4" boiler drain connection, and two (2) RTD probes on recirculation loop tie-in and a 2" check valve on each cold water inlet with inlet RTD probes and pressure sensors and full port ball valves on the hot and cold inlets.